

Product Configuration



Input Options

| | | |
|---|---------------------------------------|----------|
| 1 | Platen Cover | KA1640PC |
| 2 | Automatic Document Feeder (100-Sheet) | MR2020 |
| 3 | Paper Feed Unit (250-Sheet) | MY1038 |

Memory Options

| | | |
|---|--------------|--------|
| 4 | 64 MB Memory | GC1240 |
|---|--------------|--------|

Other Options

| | | |
|---|---------------------------------|-------------|
| 5 | Harness Kit for Coin Controller | GQ1130 |
| 6 | Stand | STAND000100 |

Supplies

| | |
|-----------|------------------------|
| Toner | T2450 |
| Developer | 6LA27715000 (D-2320) |
| Drum | 41303611000 (OD-1600S) |

Base Machine Dimensions (W x D): 23.6" x 25.3"

Power Supply: 115 Volts / 12 Amps