

Your office never looked
more productive.

Medium Workgroup



e-STUDIO™ 170F

TOSHIBA
Leading Innovation >>>



17



Workgroup



Black & White



The Toshiba e-STUDIO170F is a hardworking facsimile system that helps make small and medium sized workgroups more productive. This multifunction unit can fax, print, copy and scan—faxing at an impressive rate of 3 seconds per page and printing at 17 pages per minute. Small and compact, the e-STUDIO170F is the perfect solution where space is limited.

- e-STUDIO170F** - 17 PPM Laser Fax Machine, 33.6 Kbps (110V)
- e-STUDIO170F220V** - 17 PPM Laser Fax Machine, 33.6 Kbps (220V)
- MY1025** - 500-Sheet Cassette
- GJ1110** - Handset
- OD170F** - Drum Unit
- ZT170F** - Toner

FEATURES

Fax Features

- Super G3, 33.6 Kbps Modem Speed
- 17 PPM Print Speed
- 3 Seconds Per Page Transmission
- 3 Second Quick Scan
- JBIG Compression
- 128 Level Gray Scale

Dialing Features

- 38 Programmable One-Touch Keys
- 150 Abbreviated/Alphabet Dials
- 188 Location Autodialer
- Automatic Redial
- Chain Dial
- Group Dialing (50 Groups)
- Multi-Key (Up to 100 manually dialed locations plus autodialer locations)

Transmission Features

- Auto/Manual Contrast Control
- Delayed Transmission (Up to 31 days)
- Direct Send Transmission
- Error Correction Mode (ECM)
- ITU-T Relay Transmission
- ITU Sub-Address Transmission
- Manual Broadcast
- Memory Transmission
- Multi-Location/Broadcast Transmission
- Polling (Simple, Secure, Delayed, Multi-Address)
- Priority Transmission (Up to 24 Hours)
- Recovery Transmission
- Reservation Transmission
- Smart Batching

Reception Features

- Automatic Legal to Letter Reduction
- FAX/TAD Auto Switch
- TEL/FAX Auto Switch
- Memory Reception
- Secure Reception

Memory Features

- 7 MB Memory (Approximately 700 pages)*
- Memory Backup (1 Hour)
- Memory Release
- Memory Overflow Protection
- Multi-Memory Access

Multifunction Features

- Optional PC Faxing
- Single or Multi Copy (Up to 99 sequential)
- TWAIN Scanning
- 600 dpi Windows® Printing
- Convenience Copy
- Compact Footprint
- Device Setup

Management Features

- Account Codes
- Department Codes (50)
- Confirmation Reports (With reduced image of 1st page)
- Power Save Mode
- Remote Terminal Identification (Display/Print)

Paper Handling

- 40-Sheet Automatic Document Feeder
- Collated Printing
- Letter or Legal Sheet Output Capabilities
- Single Sheet Bypass
- 250-Sheet Paper Cassette

SPECIFICATIONS

Useable Circuits

- Compatibility**
- Modem Speed (Kbps)**
- Data Compression**
- Transmission Speed**
- Page Memory**
- Memory Backup**
- Fax Resolution**

Public Switch Telephone Network (PSTN)
ITU-T Group 3, Super G3, ECM
33.6/28.8/14.4/9.6/7.2/4.8/2.4 Kbps
MH/MR/MMR/JBIG
Approx. 3 Seconds Per Page* (ECM)
7 MB (Approx. 700 pages)*
1 Hour
Standard Mode: 203 pels/in. x 98 lines/in.
(8 pels/mm x 3.85 pels/mm)
Fine Mode: 203 pels/in. x 196 lines/in.
(8 pels/mm x 7.7 pels/mm)
Ultra Fine Mode: 406 pels/in. x 391 lines/in.
(16 pels/mm x 15.4 pels/mm)

- Scanning Method**
- Gray Scale**
- Automatic Document Feeder**
- Scanning Speed**
- Effective Scanning Width**
- Contrast Control**

Contact Image Sensor (CIS)
128 Levels
40 Sheets

- Printing Method**
- Print Speed**
- Printing Resolution**
- Paper Supply**

3 Seconds Per Page Quick Scan*
Up to 8.4" (214 mm)
Automatic and 3 Step Selectable (Normal/Darker/Lighter)
Monochrome Laser
17 PPM
Print/Copy: 600 x 600 dpi
Standard: 250 Cut Sheet Plain Paper (Letter/Legal)
Optional: 500 Sheets (Letter)
Letter or Legal
150 Sheets

- Recording Paper Size**
- Receiving Paper**
- Output Tray**
- Connections**

RJ11 Telephone Jack
USB 2.0 Interface (Printing/Scanning)
Windows® 98 SE, 2000, Me, XP, Server 2003
110 VAC, 50/60 Hz
21.3"(W) x 19.7"(D) x 23.6"(H)
541mm x 500mm x 599mm
35.3 lbs. (16 kg)

- Operating Systems**
- Power Requirements**
- Dimensions**

Weight

* ITU Testchart #1, Standard Resolution.

Corporate Office: 2 Musick, Irvine, California 92618-1631
East Coast: 959 Route 46 East, 5th Floor, Parsippany, New Jersey 07054
Tel: 973/316-2700 Fax: 973/263-2393
Midwest: 8770 W. Bryn Mawr Avenue, Suite 700, Chicago, Illinois 60631
Tel: 773/380-6000 Fax: 773/380-8077
South: 4855 Peachtree Industrial Blvd., Suite 210, Norcross, Georgia 30092-3024
Tel: 770/209-8540 Fax: 770/209-8556
West Coast: 142 Technology, Suite 150, Irvine, California 92618
Tel: 949/462-6262 Fax: 949/462-2700
Web Site: www.copiers.toshiba.com or www.fax.toshiba.com
© 2005 Toshiba America Business Solutions, Inc., Electronic Imaging Division
e-STUDIO170F Specification Sheet/Inv. Code ES170F2

Designs and specifications subject to change without notice. Actual specifications based on engine design and may vary according to usage and environment. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Driver and connectivity feature support varies by client/network operating system. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability.

AUTHORIZED TOSHIBA DEALER