TOSHIBA

C-STUDIO[®] 2510AC series

- > Color Multifunction Printer
- > Up to 25 PPM
- > Small Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Customizable UI



CONNECT, INTEGRATE, SIMPLIFY, AND MORE.

Technology for every workplace; delivering advanced functionality, ease of use, and peace of mind. Every business is unique. That's why Toshiba offers the latest customizable solutions that can be tailored to meet your needs. Toshiba solutions help you simplify complex tasks while managing diverse information—

efficiently and safely to maximize your productivity.

Toshiba's latest series delivers on our commitment to collaborate with clients to provide tailored, cost-effective solutions that meet your print, document management, and content needs while helping you to meet your green objectives.

- > 20 & 25 PPM
- > Affordable, high-resolution color
- > High-volume black & white and color
- > Advanced e-BRIDGE Next technology
- > Fast dual-core processor





Simple, smart and stylish.

A larger 10.1" tablet-style touch screen with an embedded web browser is easy to use, and customizable to meet your needs, enhancing the sleek and modern look of the complete series.

Color commands attention. Technology makes it possible.

It's important that an MFP is powerful, reliable, and efficient. Add color to that and you have even more ways to make your documents impactful.

- > Up to 600 dpi x 1,200 dpi (PS3)
- > 256 gradations provide ultra-smooth transitions in photos and illustrations
- Auto-calibration ensures consistency of color across small and large print jobs

Elevate streamlines complicated multi-step processes into automated, one-touch functions.

We know you have work to do and at Toshiba we've introduced a new concept designed to make your job easier and more productive by personalizing the MFP user interface around your specific business processes.

Elevate enables customized and automated workflow presenting the user with convenient one-touch functions addressing only the tasks they use most. This results in simple operation and improved efficiency leading to an overall cost savings. Let Toshiba Elevate your productivity.

- Customize and automate workflows specifically around your business processes
- Boost productivity by reducing manual and paper intensive processes in the office
- Personalize the user interface by department to deliver the utmost efficiency
- Cost savings and greater efficiency through improved workflow and productivity
- Clear away clutter and confusion on home screen by presenting only the tasks used most

COMPACT SIZE, ALL-NEW LOOK, AND A POWERFUL PUNCH.

For small and medium businesses and workgroups that demand color along with a small footprint, Toshiba has answered the call. The e-STUDIO2510AC Series is packed with industryleading technologies and innovations designed to help workgroups connect, integrate and simplify.

Print Around eliminates printing bottlenecks by allowing other print jobs to go around a job that's held-up for a specific paper size, media type or even color toner.

Job Reservation will queue up multiple copy or print jobs so users can send jobs whenever.

Saddle/Fold Capabilities offer saddle-stitch finishing and the option to fold without stapling.

Auto Skew Correction ensures your scanned documents using the document feeder are reproduced accurately.

Heavy-Media Duplex Support can also handle 16 lb bond to 90 lb index for heavy duty duplexing.

Print-from USB lets you print PDF and JPG files straight from your USB drive and the MFP will scale document to fit the available paper size if necessary.

e-BRIDGE Plus for USB Storage is great for capturing a file quickly when you're on the go.

Notifications Feature takes the hassle out of checking for depleted supplies or maintenance needs.

Paper Volume Indicators on the front panel make it easy to see the paper sizes, types and levels in each cassette.

Scan Preview allows you to review your scanned documents digitally, even rotate and change pages prior to sending to file or email.

Fax Preview saves valuable resources by letting you view received faxes prior to printing them.

Service Module Design significantly reduces the cost and time spent servicing the MFP.









CONVENIENCE AND SECURITY.

Small workgroups looking for quality color will appreciate that the e-STUDIO2510AC Series is easily integrated, customizable, and solutions ready, with Toshiba's Open Platform.

AirPrint[®] and Mopria[®] support address the printing needs of mobile device users, while Wi-Fi direct simplifies access to the MFP. Toshiba's exclusive e-BRIDGE Print & Capture application enables users additional printing features and the ability to scan documents back to their tablets or smart phones.

Toshiba's V4 Driver with Toshiba Print Experience serves PCL users, a universal print driver and XPS support addresses Windows[®] environments while PS3 support provides connectivity for Macintosh[®] users and beyond.

A variety of time-saving, function-adding plug-ins that enable productivity right in the driver. For instance:

- e-BRIDGE Job Point—quickly split up large jobs with up to 10 Toshiba MFPs
- e-BRIDGE Job Replicator—streamline the creation of multi-part forms and documents
- e-BRIDGE Job Separator—perform batch printing easily using any Windows[®] app
- e-BRIDGE Job Build—conveniently print different document types all together

Toshiba's new e-BRIDGE Plus apps, including e-BRIDGE Plus for OneDrive® for Business, e-BRIDGE Plus for SharePoint® Online and e-BRIDGE Plus for Exchange Online let users scan to and print from Microsoft's cloud-based services directly at the front panel of the e-STUDIO MFP or their mobile device. This includes Word,[™] Excel® and PowerPoint® (docx, xlsx, pptx) documents stored in OneDrive® accounts or SharePoint® locations. When combined with our embedded OCR feature, documents can be scanned into popular Office[™] formats as well.*

Toshiba's current e-BRIDGE multi-function printers are compatible with Microsoft Universal Print which enable customers to fully manage their print environment from Microsoft Azure. In addition, our e-BRIDGE Plus for Google Drive[™], e-BRIDGE Plus for OneDrive[®], e-BRIDGE Plus for DropBox[®], and e-BRIDGE Plus for box[™] offer scan and print solutions to the popular cloud storage destinations.*

*Your network settings and/or access control may vary depending on network environment when installing e-BRIDGE Plus applications. For details, please consult Toshiba's sales person.

Industry-Leading Security

Along with all of the new and innovative Toshiba technologies, we regard the security of your business a top priority.

- A 320GB Self-Encrypting Drive (SED) with Automatic Data Invalidation (ADI) & Data Overwrite capability provides top level security
- Available FIPS 140-2 Validated SED meets and exceeds strict government requirements
- IPsec is available to securely encrypt data sent to and from the MFP

Environmental Protection

Innovation that is truly innovative makes certain that our environment is part of the equation, which is precisely what we do here at Toshiba.

- > ENERGY STAR® V3.0 certified
- RoHS compliance, the use of recycled plastics, and Super Sleep (0.6W) Mode work to help the environment
- EPEAT Gold Registered for greener electronics, designed to help purchasers choose products that reduce environmental impact
- The new e-STUDIO models' Typical [weekly] Electrical Consumption or TEC value is exceptionally low, equating to an environmentally friendly product with a low operating cost
- e-BRIDGE Plus for Green Information provides users with a graphical display at the MFP of their environmental contribution to promote more effective use



FEATURES, BENEFITS, AND THE WOW FACTOR.

1 Document Feeder Options

MR3031B Reversing Automatic Document Feeder (RADF) KA5005PC Platen Cover

2 Accessory Tray & Options

GR1330	Accessory Tray
GR9000	Bluetooth Keyboard
GR1340	10-Key Numeric Keypad

3 Finishing Options

MJ1042B	50-Sheet Inner Finisher
MJ1110B	50-Sheet Saddle-Stitch Finisher
MJ5014	Job Separator

4 Additional Paper Options

KD105B8	Paper Feed Pedestal
KD1059B	2,000-Sheet Large Capacity Feeder
MY1048B	Additional Drawer Module for PFP
MY1049B	Envelope Cassette



Additional Option Highlights

- > Multi-Station Print Enabler
- > Embedded OCR Enabler
- > Wireless LAN/Bluetooth
- IPsec Security Enabler
- Single & Dual-Line Facsimile
- Hidden Card Reader Pocket

The Toshiba e-STUDIO2510AC Series can increase the efficiency of your workgroups, improve the professionalism of your presentations, and streamline the workflow of your organization. And, that's just for starters.

Touch and Swipe with Ease

An easy-to-use, tablet style 10.1" color touch screen panel works intuitively, helping you find instructions, functions, and commands with the swipe of the finger.

Multi-Station Print Enabler

Toshiba's internally developed Multi-Station Print Enabler allows users to send print jobs from their desktop and retrieve them at any convenient MFP by simply swiping their card and authenticating at that device.

A Clever Inside Pocket

We've put the Authentication Card Reader inside the machine for a cleaner look.

Envelopes—the Perfect Fit

A special envelope cassette is available to hold up to 60 envelopes, making sure each one is fed and printed in the same place, every time.

Volumes and Volumes

A high monthly copy volume up to 84,000 pages. Toner yields are 33,600 CMY and 38,400 K pages (at 5%) respectively.

Advanced e-BRIDGE Next Technology

Built on Linux[®], this latest e-BRIDGE Next architecture features an Embedded Web Browser, a dual-core processor, up to 4GB RAM and a 320GB SED enabling the MFP to easily drive Toshiba's internally developed solutions or even third-party applications.

C:studio[®] 2010ac/2510ac

Main Specifications

Copy System	Indirect Electrostatic Photographic Method/OPC/LED Printing/
	Heat Roller Fusing
Display	10.1" Color WSVGA Touch Screen Tilting Display
Copy Speed	20/25 PPM (LT)
First Copy Out	Color: 9.5/9.5 Seconds
	Monochrome: 7.1/7.1 Seconds
Warm-Up Time	Approx, 21 Seconds
Copy Resolution	600 x 600 dpi
Stack Feed Bypass	ST-R to LD, Envelope
Multiple Copying	Up to 999 Copies
Paper Capacity	Standard 350 Sheets/Max. 2,900 Sheets
Original Feed	Optional 100-Sheet RADF
	RADF Scan: Up to 73 IPM (Monochrome or Color), Simplex: 9.3-41.8 lb Bond,
Scan Speed & Weights	
May Original Size	Duplex: 13.3-41.8 lb Bond
Max. Original Size	
Paper Feed Sizes	Drawer 1: 250 Sheets-ST-R to LD
	Stack Feed Bypass: 100 Sheets-3.9" x 5.8" to LD
	Opt. Paper Feed Unit: 550 Sheets-ST-R to LD
	Opt. 550-Sheet Paper Feed Pedestal-ST-R to LD
	Opt. 550-Sheet Drawer for PFP-ST-R to LD
	Opt. Envelope Cassette for PFP-Approx. 60 Envelopes/550 Sheets-ST-R to LG
	Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-LT Only
Paper Weights	Standard: 250 Sheets-16 lb Bond-90 lb Index
	Stack Feed Bypass: 100 Sheets-16 lb Bond-110 lb Index
	Opt. Paper Feed Unit: 550 Sheets-16 lb Bond-90 lb Index
	Opt. 550-Sheet Paper Feed Pedestal: 16 lb Bond-90 lb Index
	Opt. 550-Sheet Drawer for PFP: 16 lb Bond-90 lb Index
	Opt. Envelope Cassette for PFP: 16 lb Bond-90 lb Index
	Opt. 2,000-Sheet Tandem LCF (Pedestal Type): 17-28 lb Bond
Duplex	Standard Automatic Duplex Unit: 16 lb Bond-90 lb Index
Reproduction Ratio	25% to 400%
Max Duty Cycle	Max. 67.2K Month (e-STUDIO 2010AC)
max 2 aty eyere	Max. 84K Month (e-STUDIO 2510AC)
Weight	Approx. 126 lb
Approx. Dimensions	22.6" (W) x 23" (D) x31" (H)
CMYK Toner Yield	CMY: 33.6K, BK: 38.4K @ 5%
Power Source	120 Volts, 50/60 Hz, 12 Amps
Power Consumption	Maximum 1.5kW (120V)
CPU	Intel Atom™ 1.33GHz (Dual-Core)
Memory	2GB, Max. 4GB
Hard Disk Drive	320GB Self-Encrypting Drive

e-BRIDGE Next Print Specifications

PDL Print Speed Print Resolution Operating Systems	PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG 20/25 Pages Per Minute (LT) 600 x 600 dpi (5 bit) 600 x 1,200 dpi (1 bit) PS3 Only Windows® 8.1,10, Windows Server® 2012/R2, Windows Server® 2016,
	Macintosh® (macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, 10.12, 10.13, 11.4), Unix®. Linux®
Network Protocols	TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for Novell® Environments, EtherTalk for Macintosh® Environments
Printing Protocols	SMB, LPR/LPD, IPP (Ver.2.0) w/Authentication, AppleTalk [®] PAP or EtherTalk, Port 9100 (Bi-Directional), NetWare P-SERVER LPD w/ iPrint, WS Print, FTP
Print Drivers	Windows [®] 8.1 (32-bit, 64-bit), Windows Server [®] 2012/R2 (64-bit), Windows Server [®] 2016, Windows [®] 10 (32-bit, 64-bit), macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, 10.12, 10.13, 11.4
Interface	RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-Speed), Optional 802.11b/g/n, Wireless LAN, Optional Bluetooth
Wireless Device	AirPrint [®] , Mopria [®] , e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple [®] App Store or Google Play)
Device Management	TopAccess, EFMS 6.30 (e-BRIDGE Fleet Management Software)
Account Control	Up to 10,000 Users or 1,000 Departments Supports User Authentication (on Device), Login Name/Password (via Windows [®] Domain) or Login Name/ Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function
Accessibility Features	Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen

Timeout and Audible Beep Message Alerts

Wi Fi

-	Security Features	User Authentication, On-Board Data Scramble Function, SCEP, Disable
		e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC
		Address Filtering (10 Sets), Network Service Control, Network Port Control,
		SMB Packet Signing, SSL/TLS (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS,
		SYSLOG), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified
		(ISO/IEC15408)* with HCD-PP v1.0, IEEE802.1X (Wired/Wireless), Digital
		Signature for Client Utilities, Password Policy, Password Lock, Password
		Expiration, Self Testing, Job Access Control, Log Access Control for Job
		Log, Security Stamp, Role Based Access Control, Secure PDF, Digital
		Signature for Firmware Update, Integrity Check Function, Image Log, Card
		Authentication, NFC Authentication
		*Conformance with HCD-PPv1.0 in High Security Mode.
	Environmental Stds.	ENERGY STAR® (V3.0), EPEAT Gold
	Certification	WHQL (Windows [®] 8.1, 10, 2008 R2, 2012, 2012 R2, 2016, 2019), Novell [®] ,
		Citrix [®] , SAP, AirPrint [®] and Mopria [®]

Scan Specifications

Scan Speed Scan Modes	RADF Scan: Up to 73 IPM (Monochrome or Color) Standard: Full Color, Auto Color, Monochrome, Grayscale
Scan Resolution	600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi
File Formats	Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.) Color/Grayscale: JPEG, TIFF-Multi/Single Page, PDF-Multi/Single Page, Sim PDF, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.)
Image Compression	Color/Grayscale: JPEG (High, Middle, Low)

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	Up to 33.6 Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations /Job
Scan Speed	0.7 Seconds Per Page, Maximum 73 IPM

e-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder/Box,
	200 Pages Per Document

Accessories (Options)

mopria

Apple AirPrint

			0.04000
Platen & Document Feeder C		Card Reader Holder	GR1320
RADF	MR3031	4GB Memory Option	GC1410
Platen Cover	KA5005PC	FIPS HDD	GE1230
Additional Paper Options		Meta Scan Enabler	GS1010
Paper Feed Pedestal	KD1058	IPsec Enabler	GP1080
Paper Feed Unit	MY1047	Unicode Font Enabler	GS1007
Drawer Module	MY1048	Embedded OCR Enabler	
Envelope Cassette Option	MY1049	Per Seat License	GS1080NODE
Large Capacity Feeder	KD1059LB	Multi-Station Print Enabler	
Earge eapaoity receasi	RETOCOLE	Per Seat License	GS1090NODE
Finishing Options		e-BRIDGE Plus for OneDrive	
Inner Finisher	MJ1042B	for Business V3.0	GB2300NODE
Saddle-Stitch Finisher	MJ1110B	e-BRIDGE Plus for Sharepoint	
Hole Punch Unit (For MJ1042)	MJ6011	Online V3.0	GB2310NODE
Hole Punch Unit (For MJ1110)	MJ6105	e-BRIDGE Plus for Exchange	
Bridge Kit	KN5005	Online V3.0	GB2320NODE
Job Separator	MJ5014	External Interface Enabler	GS1020
Connectivity/Security Option		Miscellaneous Options	
FAX Unit/2nd Line for FAX Unit	GD1370N	Stand	STAND5005
FAX Over IP License Key	GS1100NODE		
Wireless LAN/Bluetooth	GN4020	Accessible Arm	KK2550
Bluetooth Keyboard	GR9000	Work Tray	KK5005
Accessory Tray	GR1330	Manual Pocket	KK5008

GR1340

Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

Ν

Rh

@ 2021 Toshiba America Business Solutions, Inc. Electronic Imaging Division Inv. Code 22335 $\,$ 2510AC Series Brochure $\,$ 5K PG 10/21 $\,$

Corporate Office
East Coast
Midwest
South
West Coast
Wab Sita

Panel 10-Key Option

25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000 959 Route 46 East, 5th Floor, Parsippany, NJ 07054
Tel: 973-316-2700 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631
Tel: 773-380-6000
2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000
www.business.toshiba.com

Harness Kit for Coin Controller

GQ1280