

TOSHIBA

e-STUDIO™ 2823AM

- > Black & White Multifunction Printer
- > Up to 28 PPM
- > Small Workgroup
- > Copy, Print, Scan
- > Network Ready

Multifunction versatility meets a compact footprint with the new Toshiba e-STUDIO2823AM. Impressive black and white output with crisp 2,400 x 600 dpi images delivered at up to 28 pages per minute and full-color scans at 22 pages per minute help your office run at peak efficiency. Utilize a variety of media in different sizes with a standard 250-sheet cassette, 100-sheet bypass, and optional 250-sheet cassette. The busiest of small businesses can take advantage of additional savings with easy two-sided copying and printing thanks to an optional Reversing Automatic Document Feeder (RADF) and Automatic Duplex Unit (ADU).



Specifications

Copying/Printing Process Type	Indirect Electrostatic Photographic Method Desktop
Original Scanning Method	Contact Image Sensor (CIS)
Resolution	2400 x 600 dpi (with Smoothing)
Gradation	256 Steps
Original Platen Type	Fixed Hard Platen, Optional 50-Sheet RADF (14-28 lb)
Available Original Size	ST-R to LD
Available Paper Size	Drawer: ST-R to LD Stack Feed Bypass: ST-R, LT, LD, Envelope
Paper Supply	Standard: Drawer (250 Sheets x 1) Stack Feed Bypass (100 Sheets) Max.: 600 (Optional 250 Sheets x 1)
Available Paper Weight	Drawer: 17-20 lb (Including Optional Paper Sources) Stack Feed Bypass: 14-120 lb Index Auto Duplexing Unit: 17-20 lb
Paper Exit	Face Down/Inner Tray
Warm-up Time	Approx. 18 Seconds (Scanner Function Available During Warm-Up)
Counter	Electronic Counter (Indication by LCD Display)
Memory	512 MB
Department Codes	100
Power Supply	115 Volts, 12 Amps
Power Consumption	Maximum: 1.5kW
TEC Value	1.36 kWh/week
Dimensions	Standard: Approx. 22.6" x 21.2" x 16" (W x D x H) With PFU: Approx. 23" x 22.2 x 20" (W x D x H)
Weight	Approx. 59.4 lb
Special Features	Energy Saver, Auto Sleep Mode, Department Code
Max Duty Cycle	64K Copies
Certifications	Energy Star V3.0, EPEAT (GOLD) & WEE (Argentina Model) + RoHS Compliant
Worldwide Safety Stds.	UL, GS, CE, CDRH, SASO, IRAM, EAC, CCC
Black Toner Yield	17.5K Impressions @ 5%

Copy Specifications

Copying Speed	28 PPM
Original Scan Speed	25 SPM (by Using RADF)
Scan Resolution	600 x 600 dpi (for Copying)
First Copy Time	Less Than 6.5 Seconds
Original/Copy Size	ST-R to LD
Original Mode	Photo, Text/Photo, Text, Background Erase
Image Density Control	Automatic/Manual (11 Steps)
Reproduction Ratio	Zoom: 25% to 400% in 1% Increments
Multiple Copying	Up to 999 Copies (Ten Key Input)
Special Features	Department Codes (100) Interrupt, APS/AMS, Auto Job Start, Automatic Sort Mode, ID Card Copy, One Touch Keys (2)



Print Specifications

Printing Speed	28 PPM
Printing Resolution	2400 x 600 dpi (with Smoothing)
Interface	Standard: 10/100 Base-T, USB 2.0
Driver	GDI
USB Direct Printing	JPEG, TIFF, PDF (Only PDF created by MFP can be printed)
Support OS	Windows 7, 8, 8.1, 10, 2008R2, 2012, 2012 R2, (WHQL), CUPS PCL Unix, Linux 5.10.x, 6.5.x

Scan Specifications

Connection Type	Standard: USB 2.0
Scanning Resolution	100/150/200/300/400/600 dpi
Scanning Speed	25 SPM (BW) at 600 dpi, 22 SPM (Color) @ 200 dpi, 13 SPM @ 300 dpi
Scan Agent	Scan to USB, TWAIN

Paper Handling

Reversing Automatic Document Feeder (RADF)

Stack Capacity	50 Sheets
Original Setting	Face Up
Original Paper Size	ST-R to LD
Original Paper Weight	14-28 lb

Options

Platen Cover	KA2507
Reversing Automatic Document Feeder (RADF)	MR3032
Paper Feed Unit (PFU)	MY1043B
Cabinet	STAND2507
Automatic Duplexing Unit (ADU)	MD0107
Damp Heater (for Drum)	MF2505U
Harness for Coin Controller	GQ1131

Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

Corporate Office

East Coast

Midwest

South

West Coast

Web Site

25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000
959 Route 46 East, 5th Floor, Parsippany, NJ 07054
Tel: 973-316-2700
8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631
Tel: 773-380-6000
2037 Bakers Mill Rd., Dacula, GA 30019
Tel: 678-546-9385
25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000
www.business.toshiba.com