

# TOSHIBA

## e-STUDIO™ 2803AM

- > Black & White MFP
- > 28 PPM
- > Small Workgroup
- > Copy, Print, Scan
- > Network Ready

The new Toshiba e-STUDIO2803AM combines a small footprint with multifunction versatility. It combines copy and network print capability at up to 28 pages per minute at a crisp 2,400 x 600 dpi and full color scanning at up to 22 pages per minute. A standard 250-sheet cassette and 100-sheet bypass provide support for a wide range of media from Statement to Ledger-size with an optional 250-sheet cassette for busier office environments. An optional Reversing Automatic Document Feeder (RADF) and Automatic Duplex Unit (ADU) enable easy two-sided copying and printing that save money and resources.



## Specifications

<b>Copying/Printing Process</b>	Indirect Electrostatic Photographic Method
<b>Type</b>	Desktop
<b>Original Scanning Method</b>	Contact Image Sensor (CIS)
<b>Resolution</b>	2400 x 600 dpi (with Smoothing)
<b>Gradation</b>	256 Steps
<b>Original Platen Type</b>	Fixed Hard Platen, Optional 50-Sheet RADF (14-28 lb)
<b>Available Original Size</b>	ST-R to LD
<b>Available Paper Size</b>	Drawer: ST-R to LD Stack Feed Bypass: ST-R, LT, LD Envelope
<b>Paper Supply</b>	Standard: Drawer (250 Sheets x 1) Stack Feed Bypass (100 Sheets) Max.: 600 (Optional 250 Sheets x 1)
<b>Available Paper Weight</b>	Drawer: 17-20 lb (Including Optional Paper Sources) Stack Feed Bypass: 14-120 lb Index Auto Duplexing Unit: 17-20 lb
<b>Paper Exit</b>	Face Down/Inner Tray
<b>Warm-up Time</b>	Approx. 18 Seconds (Scanner Function Available During Warm-Up)
<b>Counter</b>	Electronic Counter (Indication by LCD Display)
<b>Memory</b>	512 MB
<b>Department Codes</b>	100
<b>Power Supply</b>	115 Volts, 12 Amps
<b>Power Consumption</b>	Maximum: 1.5kW
<b>Dimensions</b>	Standard: Approx. 22.6" x 21.2" x 16" (W x D x H) With PFU: Approx. 23" x 22.2" x 20" (W x D x H)
<b>Weight</b>	Approx. 59.4 lb
<b>Special Features</b>	Energy Saver, Auto Sleep Mode, Department Code
<b>Max Duty Cycle</b>	64K Copies
<b>Certifications</b>	Energy Star V3.0, EPEAT (GOLD) & WEE (Argentina Model) + RoHS Compliant
<b>Worldwide Safety Stds.</b>	UL, GS, CE, CDRH, SASO, IRAM, EAC, CCC
<b>Black Toner Yield</b>	14.6K Impressions @ 6%

## Copy Specifications

<b>Copying Speed</b>	28 PPM
<b>Original Scan Speed</b>	25 SPM (by Using RADF)
<b>Scan Resolution</b>	600 x 600 dpi (for Copying)
<b>First Copy Time</b>	Less Than 6.5 Seconds
<b>Original/Copy Size</b>	ST-R to LD
<b>Original Mode</b>	Photo, Text/Photo, Text, Background Erase
<b>Image Density Control</b>	Automatic/Manual (9 Steps)
<b>Reproduction Ratio</b>	Zoom: 25% to 400% in 1% Increments
<b>Multiple Copying</b>	Up to 999 Copies (Ten Key Input)
<b>Special Features</b>	Department Codes (100), APS/AMS, Auto Job Start, Automatic Sort Mode, ID Card Copy, One Touch Keys (2)



## Print Specifications

<b>Printing Speed</b>	28 PPM
<b>Printing Resolution</b>	2400 x 600 dpi (with Smoothing)
<b>Interface</b>	Standard: 10/100 Base-T, USB 2.0
<b>Driver</b>	GDI
<b>USB Direct Printing</b>	JPEG, TIFF, PDF (Only PDF created by MFP can be printed)
<b>Support OS</b>	Windows 7, 8, 8.1, 10, 2008R2, 2012, 2012 R2

## Scan Specifications

<b>Connection Type</b>	Standard: USB 2.0
<b>Scanning Resolution</b>	150/200/300/400/600 dpi
<b>Scanning Speed</b>	25 SPM (BW) at 600 dpi, 22 SPM (Color) @ 200 dpi, 13 SPM @ 300 dpi
<b>Scan Agent</b>	Scan to USB, TWAIN

## Paper Handling

### Reversing Automatic Document Feeder (RADF)

<b>Stack Capacity</b>	50 Sheets
<b>Original Setting</b>	Face Up
<b>Original Paper Size</b>	ST-R to LD
<b>Original Paper Weight</b>	14-28 lb

### Options

<b>Platen Cover</b>	KA2507
<b>Reversing Automatic Document Feeder (RADF)</b>	MR3029
<b>Paper Feed Unit (PFU)</b>	MY1043
<b>Cabinet</b>	STAND2507
<b>Automatic Duplexing Unit (ADU)</b>	MD0107
<b>Damp Heater (for Drum)</b>	MF2505U
<b>Harness for Coin Controller</b>	GQ1131

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.