

TOSHIBA

e-STUDIO™ 2803AM

- > Black & White MFP
- > 28 PPM
- > Small Workgroup
- > Copy, Print, Scan
- > Network Ready

The new Toshiba e-STUDIO2803AM combines a small footprint with multifunction versatility. It combines copy and network print capability at up to 28 pages per minute at a crisp 2,400 x 600 dpi and full color scanning at up to 22 pages per minute. A standard 250-sheet cassette and 100-sheet bypass provide support for a wide range of media from Statement to Ledger-size with an optional 250-sheet cassette for busier office environments. An optional Reversing Automatic Document Feeder (RADF) and Automatic Duplex Unit (ADU) enable easy two-sided copying and printing that save money and resources.



Specifications

Copying/Printing Process	Indirect Electrostatic Photographic Method
Type	Desktop
Original Scanning Method	Contact Image Sensor (CIS)
Resolution	2400 x 600 dpi (with Smoothing)
Gradation	256 Steps
Original Platen Type	Fixed Hard Platen, Optional 50-Sheet RADF (14-28 lb)
Available Original Size	ST-R to LD
Available Paper Size	Drawer: ST-R to LD Stack Feed Bypass: ST-R, LT, LD Envelope
Paper Supply	Standard: Drawer (250 Sheets x 1) Stack Feed Bypass (100 Sheets) Max.: 600 (Optional 250 Sheets x 1)
Available Paper Weight	Drawer: 17-20 lb (Including Optional Paper Sources) Stack Feed Bypass: 14-120 lb Index Auto Duplexing Unit: 17-20 lb
Paper Exit	Face Down/Inner Tray
Warm-up Time	Approx. 18 Seconds (Scanner Function Available During Warm-Up)
Counter	Electronic Counter (Indication by LCD Display)
Memory	512 MB
Department Codes	100
Power Supply	115 Volts, 12 Amps
Power Consumption	Maximum: 1.5kW
Dimensions	Standard: Approx. 22.6" x 21.2" x 16" (W x D x H) With PFU: Approx. 23" x 22.2" x 20" (W x D x H)
Weight	Approx. 59.4 lb
Special Features	Energy Saver, Auto Sleep Mode, Department Code
Max Duty Cycle	64K Copies
Certifications	Energy Star V3.0, EPEAT (GOLD) & WEE (Argentina Model) + RoHS Compliant
Worldwide Safety Stds.	UL, GS, CE, CDRH, SASO, IRAM, EAC, CCC
Black Toner Yield	14.6K Impressions @ 6%

Copy Specifications

Copying Speed	28 PPM
Original Scan Speed	25 SPM (by Using RADF)
Scan Resolution	600 x 600 dpi (for Copying)
First Copy Time	Less Than 6.5 Seconds
Original/Copy Size	ST-R to LD
Original Mode	Photo, Text/Photo, Text, Background Erase
Image Density Control	Automatic/Manual (9 Steps)
Reproduction Ratio	Zoom: 25% to 400% in 1% Increments
Multiple Copying	Up to 999 Copies (Ten Key Input)
Special Features	Department Codes (100), APS/AMS, Auto Job Start, Automatic Sort Mode, ID Card Copy, One Touch Keys (2)



Print Specifications

Printing Speed	28 PPM
Printing Resolution	2400 x 600 dpi (with Smoothing)
Interface	Standard: 10/100 Base-T, USB 2.0
Driver	GDI
USB Direct Printing	JPEG, TIFF, PDF (Only PDF created by MFP can be printed)
Support OS	Windows 7, 8, 8.1, 10, 2008R2, 2012, 2012 R2

Scan Specifications

Connection Type	Standard: USB 2.0
Scanning Resolution	150/200/300/400/600 dpi
Scanning Speed	25 SPM (BW) at 600 dpi, 22 SPM (Color) @ 200 dpi, 13 SPM @ 300 dpi
Scan Agent	Scan to USB, TWAIN

Paper Handling

Reversing Automatic Document Feeder (RADF)

Stack Capacity	50 Sheets
Original Setting	Face Up
Original Paper Size	ST-R to LD
Original Paper Weight	14-28 lb

Options

Platen Cover	KA2507
Reversing Automatic Document Feeder (RADF)	MR3029
Paper Feed Unit (PFU)	MY1043
Cabinet	STAND2507
Automatic Duplexing Unit (ADU)	MD0107
Damp Heater (for Drum)	MF2505U
Harness for Coin Controller	GQ1131

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.