

Leading Innovation >>>

- > Black & White MFP
- > Up to 85 PPM
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered*



©-STUDIO 557/657/757/857

Power, performance and drive.

Toshiba introduces an impressive new lineup capable of performing flawlessly, time after time after time. The new e-STUDIO857 series boasts speeds up to 85 pages per minute using the latest generation e-BRIDGE platform to offer world-class functionality,

dependability and productivity.

Go the distance, and then some.

Step up to the e-STUDIO857 series, take a look at the easy-to-navigate, 9" color touch screen, and you'll be impressed right away. Add to that a first copy out time under 3.5 seconds and speeds from 55 to 85 crisp pages per minute at a precise 2,400 x 600 dpi that keeps going for up to 600,000 copies per month, 7,600 sheets at a time. Change toner on the fly, and print on the go. You name it. You're sure to find it here.

The central hub.

Outstanding image quality at breakneck speeds and extra high volume are perfect for growing companies and large workgroups. It is literally the central hub of all that is document related – the ultimate in storage, management and production with total network connectivity. Need help? Just push a button and you have instant access to context sensitive help straight from the user's manual.



©-STUDIO 557/657/757/857

Innovative technology for your entire network.

The new e-STUDIO857 series is versatile, capable, reliable and downright phenomenal. If you've never used a machine of this caliber, you'll be amazed at what a difference it can make in the way you do business.

Brilliant innovations made easy.

Toshiba's latest e-BRIDGE technology makes it easy to integrate business applications, multiple devices and vendor solutions. Periodic maintenance is made simple, too, thanks to an innovative service module design that allows modules to quickly and easily be removed, serviced and replaced as needed. You can also administer the entire fleet from a single location and govern access to information and functionality wherever necessary. Advanced technology is more accessible than ever.

An abundance of impressive options.

Choose from several finishers according to your document usage. The e-STUDIO857 series is available with a 50-Sheet Finisher, a 50-Sheet Finisher with Saddle-Stitch or a 100-Sheet Finisher with Saddle-Stitch. Select a 2/3-Hole Punch or Post Inserter and add pre-printed covers or inserts for precise, consistent and professional looking documents. Whether you want to impress employees or win over new clients, the e-STUDIO857 series has what it takes.

- > Superb Image Quality
- > e-BRIDGE Technology
- > Universal Print Driver
- > Fast First Copy Out Times
- > Up to 7,600 Capacity
- > Service Module Design
- > Saddle-Stitch Finisher
- > 2/3-Hole Punch
- > Post Inserter











High quality output, page after page, combined with finishing options help you create professional looking documents with ease.



Safety, security and environmental responsibility.

The increasing demands of data security and environmental safety are continually being met, and exceeded, here at Toshiba. That's because we have been ahead of the curve with regard to impending concerns and have continually applied innovative technology in order to address them.



The security of leading technology.

There is no such thing as being too careful when it comes to the security of your data and your business. That's why we've incorporated safeguards such as a new 320GB FIPS 140-2 Validated Self-Encrypting Drive (SED) with Data Overwrite. In addition, there is an IPsec option to encrypt data being sent to or from the MFP, as well as Hard Copy Security that's available to prevent the copying of sensitive documents.

Safer, smarter and greener.

As a company, we continue to invent ways in which we can reduce the environmental impact of our manufacturing processes and our products themselves. The Toshiba e-STUDIO857 series has a low power sleep mode that meets the stringent requirements of Energy Star Tier 2. It is also RoHS compliant, and even uses recycled plastics. Because of this and other eco-friendly features, the Toshiba e-STUDIO857 series is EPEAT Registered* in the greener electronics global registry developed to help purchasers choose products that reduce environmental impact. All combined, it's Toshiba's leading innovation at its greenest.





Features and benefits galore.

Here's what Toshiba's e-STUDIO857 series has to offer. You couldn't ask for more.



Pacesetting printing

Choose your speed, from 55 to 85 pages per minute. First copy out times are under 3.5 seconds for the e-STUDIO757/857 and under 4 seconds for the e-STUDIO557/657.



Reliable performance

Up to 600,000 monthly copy volume includes a toner yield that keeps pace at 73,900 pages at 6% coverage with the ability to change toner on the fly.



Broad paper handling

Take advantage of a maximum 7,600-sheet paper capacity and use up to 110 lb index from the drawers and 140 lb preprinted cover stock from the inserter.



Most advanced e-BRIDGE platform

This proprietary platform allows for improved connectivity, security and fleet management. Also, you can access third-party solutions such as PaperCut, Docuware and others – right from the front panel.



Versatile connectivity and functionality

Includes PCL6, PostScript3, and XPS as well as a Universal Printer Driver, which means you only need one driver across the entire line. Driver plug-ins enable increased functionality.



Easy to use

Scan or print directly using a USB port. A large 9" touch screen panel is easy to read and intuitive. Also, a context sensitive help button will give you added instructions as needed.



Innovative technology

Use Card Reader Support to control, cap, and accurately account for usage. Other leading innovations include Gigabit Ethernet support, e-filing for frequently reprinted jobs and an automatic OCR option for expert scanning.



Advanced finishing options

Choose from the 50-Sheet Finisher, a 50-Sheet Finisher with Saddle-Stitch or a 100-Sheet Finisher with Saddle-Stitch, not to mention 2/3-Hole Punch and Post Inserter options.



Top security

A 320GB FIPS 140-2 Validated Self-Encrypting Drive (SED) with Data Overwrite are standard. Hard Copy Security and IPsec are available as options.



Environmentally friendly

The e-STUDIO857 series is RoHS Compliant, Energy Star Tier 2 rated and EPEAT Registered* (as part of the definitive global registry for greener electronics).

E-STUDIO 557/657/757/857





- > Black & White MFP
- > Up to 85 PPM
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered*

Specifications

Memory

Drivers

Copying Process/Type IEPM (Dry Process)/Laser Technology

Original Reading Method CCD Line Sensor 2400 x 600 dpi Copy/Print Resolution Gradation 256 Steps 55/65/75/85 PPM Copy/Print Speed Warm-Up Time Approx. 130 Seconds

556/656: Less Than 4.0 Seconds (Letter-Size) First Copy Time 756/856: Less Than 3.5 Seconds (Letter-Size)

Duty Cycle 460K/515K/540K/600K Multiple Copying Up to 9.999 Copies

Standard Paper Supply 2 x 500-Sheet Drawer, 1 x 2,500-Sheet Tandem Drawer,

100-Sheet Stack Feed Bypass

Maximum Paper Supply Up to 7,600 Sheets (w/Optional 4,000-Sheet LCF)

Cassette: Statement-R to Ledger (17-110 lb) Acceptable Paper Size Bypass: Statement-R to 11" x 17" (17-110 lb)

LCF: Letter Only (17-110 lb), Tab Paper 2GB RAM, 320 GB FIPS 140-2 SED

Reduction/Enlargement 25% to 400%

100-Sheet Stack Feed Bypass Bypass Tray Control Panel 9" Wide VGA Color Touch Screen Approx. 28" x 31" x 46" (W x D x H) Dimensions

Approx. 462 lb Weiaht Power Supply 120 Volts, 20 Amps Power Consumption Maximum 2.0kW 73.9K Impressions Black Toner Yield

e-BRIDGE Print Specifications

PCL6. PostScript 3. XPS PDL Support

Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Operating Systems

NetWare 6.5, Citrix, Macintosh 10.4-10.9,

Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO Protocol Support Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1)

w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/ iPrint, Apple Talk PAP or

EtherTalk, Port 9100 (bi-directional), WS Print, FTP Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Macintosh OS 10.4-10.9

10/100/1000BaseTX Ethernet, Connectivity 802.11b/g/n, Wireless LAN, USB

Wireless Device AirPrint, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play)

Device Management Top Access.

eFMS 6.0 (e-BRIDGE Fleet Management Software)

Certification Windows 7, 8, 8.1,2008R2, 2012, 2012 R2,

WHQL, Novell, Citrix

Scan Specifications

77 SPM Color/80 SPM B&W, LT-Size @300 dpi, Scan Speed 66 SPM LT-Size @ 600 dpi (When Copying)

Scan Resolution Up to 600 dpi TIFF, PDF, JPEG, XPS, File Format

MS Word, MS Excel, Searchable PDF w/Adv. Scanning Option

Facsimile Specifications

Compatibility Super G3, G3 Data Compression MH/MR/MMR/JBIG Approx. 3 Seconds Per Page Transmission Speed Fax Modem Speed 33.6 Kbps

Transmission 500MB (HDD) Fax Memory Reception 500MB (HDD) Backup Permanent (HDD)

Memory Transmission 100 Jobs, 1,000 Destinations Max, 400 Destinations/Job

0.7 Seconds Per Page, 50 Scans Per Minute Scan Speed

Other Fax Functions Internet Fax, Network Fax

e-Filing Specifications

Operation Method Color Touch Screen Control Panel or Client PC

Number of Boxes 1 Public Box, 200 Private User Boxes

Capacity of Boxes 100 Folder Per Box

400 Documents Per Folder 1000 Pages Per Documents

Security (Standard)

Data Encryption 256 Bit AES

Meets Department of Defense (DoD) Standard 5220.22M HDD Overwrite

LDAP, SMTP, Windows Server Domain Authentication

Accessories (Options)

Additional Paper Options

4,000-Sheet LT-Size Large Capacity Feeder MP4004

Finishing Options

50-Sheet Stapler Console Finisher MJ1027 50-Sheet Saddle-Stitch Finisher MJ1028 100-Sheet Saddle-Stitch Finisher MJ1029 Rails for Finisher KN1017 2/3-Hole Punch Unit MJ6003 Post Inserter Unit MJ7001

Connectivity/Security Options

GD1350 Fax Kit 2nd Line Fax GD1260F Wireless LAN Adapter GN1060 GN3010 Antenna Advanced Scanning GB1280T IPsec Kit GP1080 Meta Scan Enabler GS1010 Harness Kit for Coin Controller GQ1240



















Corporate Office 9740 Irvine Blvd., Irvine, CA 92618-1631

Tel: 949-462-6000

959 Route 46 East, 5th Floor, Parsippany, NJ 07054 **East Coast**

Tel: 973-316-2700

Midwest 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631

Tel: 773-380-6000

South 2037 Bakers Mill Rd., Dacula, GA 30019

Tel: 678-546-9385

West Coast 9740 Irvine Blvd., Irvine, CA 92618

Tel: 949-462-6000

Web Site www.business.toshiba.com

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.

© 2014 Toshiba America Business Solutions, Inc. Electronic Imaging Division Inv. Code: 22255 557/657/757/857 Brochure 6K PG 6/14