

TOSHIBA

e-STUDIO™ 2329A/2829A

- > Black & White Multifunction Printer
- > Up to 28 PPM
- > Small Workgroup
- > Copy, Print, Scan, Fax
- > Mobile Enabled

Improve the efficiency of busy workgroups with the new Toshiba e-STUDIO2329A/2829A. Multifunctionality has never been this simple and this powerful all at once. Precise black and white output is delivered at speeds up to 28 pages per minute with full color scans at up to 22 pages per minute. The Reversing Automatic Document Feeder (RADF) and Automatic Duplex Unit (ADU) allow for two-sided copying and printing. With standard network connectivity, paper sizes supported up to 11" x 17", and a maximum paper capacity of 1,700 sheets, the e-STUDIO2329A/2829A can help get your business running even smoother. A fax feature along with a unique e-BRIDGE Print & Capture application and wireless LAN support (802.11 b/g/n) allow access and sharing from a variety of devices by authorized users.



e-STUDIO™ 2329A/2829A

Specifications

Copying/Printing Process Type	Indirect Electrostatic Photographic Method Desktop
Original Scanning Method	Contact Image Sensor (CIS)
Resolution	2400 x 600 dpi (with Smoothing)
Gradation	256 Steps
Original Platen Type	Fixed Hard Platen, Optional 50-Sheet RADF (14-28 lb)
Available Original Size	ST-R to LD
Available Paper Size	Drawer: ST-R to LD Stack Feed Bypass: ST-R, LT, LD, Envelope
Paper Supply	Standard: Drawer (250 Sheets x 1) Stack Feed Bypass (100 Sheets) Max.: 1,700 (Optional 250 Sheets x 1, 550 Sheets x 2)
Available Paper Weight	Drawer: 17-20 lb (Including Optional Paper Sources) Stack Feed Bypass: 14-120 lb Index Auto Duplexing Unit: 17-20 lb
Paper Exit	Face Down/Inner Tray
Warm-up Time	Approx. 18 Seconds (Scanner Function Available During Warm-Up)
Counter Memory	Electronic Counter (Indication by LCD Display) 512 MB (PostScript 3 Option Includes 512 MB Additional RAM)
Department Codes	100
Power Supply	115 Volts, 12 Amps
Power Consumption	Maximum: 1.5kW
TEC Value	1.17/1.36 kWh/Week
Dimensions	Standard: Approx. 22.6" x 21.2" x 16" (W x D x H) With PFU: Approx. 23" x 22.2" x 20" (W x D x H)
Weight	Approx. 59.4 lb
Special Features	Energy Saver, Auto Sleep Mode, Department Code
Max Duty Cycle	64K Copies
Certifications	Energy Star V3.0, EPEAT (GOLD) & WEE (Argentina Model) + RoHS Compliant
Worldwide Safety Stds.	UL, GS, CE, CDRH, SASO, IRAM, EAC, CCC
Black Toner Yield	17.5 Impressions @ 5%

Copy Specifications

Copying Speed	23/28 PPM
Original Scan Speed	25 SPM (by Using RADF)
Scan Resolution	600 x 600 dpi (for Copying)
First Copy Time	Less Than 6.5 Seconds
Original/Copy Size	ST-R to LD
Original Mode	Photo, Text/Photo, Text, Background Erase
Image Density Control	Automatic/Manual (11 Steps)
Reproduction Ratio	Zoom: 25% to 400% in 1% Increments
Multiple Copying	Up to 999 Copies (Ten Key Input)
Special Features	Department Codes (100) Interrupt, APS/AMS, Auto Job Start, Automatic Sort Mode, ID Card Copy, One Touch Key (2)



Print Specifications

Printing Speed	23/28 PPM
Printing Resolution	2400 x 600 dpi (with Smoothing)
Interface	Standard: 10/100 Base-T, USB 2.0 Optional: 802.11 b/g/n PCL 6 Emulation
PDL	Optional: PostScript 3 (Includes 512 MB Additional RAM)
USB Direct Printing	JPEG, TIFF, PDF (Only PDF created by MFP can be printed unless PS3 option installed)
Support OS	Windows 7, 8, 8.1, 10, 2008R2, 2012, 2012 R2, (WHQL), CUPS PCL Unix, Linux 5.10.x, 6.5.x

Scan Specifications

Connection Type	Standard: 10/100 Base-T Optional: 802.11 b/g/n
Scanning Resolution	100/150/200/300/400/600 dpi
Scanning Speed	25 SPM (BW) at 600 dpi, 22 SPM (Color) @ 200 dpi, 13 SPM @ 300 dpi
Scan Agent	Scan to File, SMB, FTP, Scan to Email, Scan to USB, TWAIN

Paper Handling

Reversing Automatic Document Feeder (RADF)

Stack Capacity	50 Sheets
Original Setting	Face Up
Original Paper Size	ST-R to LD
Original Paper Weight	14-28 lb
FAX Specifications (optional)	
Compatibility	Super G3, G3
Image Format on PSTN	JBIG, MMR, MR, MH
Document Size	ST-R-LD
Modem Speed	33.6 kbps to 2.4 kbps (Automatic Fallback)
Transmission Speed	Approx. 3 Seconds
Communication Protocols	ITU-T T.30
Memory Transmission	Max 256 Jobs, 220 Destinations/Job, 384 Pages/File
Options	
Platen Cover	KA2507
Reversing Automatic Document Feeder (RADF)	MR3032
Paper Feed Unit (PFU)	MY1043B
Paper Feed Pedestal (PFP)	KD1039B
Drawer Module	MY1044B
Cabinet	STAND2507
Fax Kit	GD1360
PostScript - e-STUDIO2309A	GA1350L
PostScript - e-STUDIO2809A	GA1350H
Wireless LAN Module	GN1100
Damp Heater (for Drum)	MF2505U
Harness for Coin Controller	GQ1131

Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. AirPrint™ and the AirPrint logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

Corporate Office

East Coast

Midwest

South

West Coast

Web Site

25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000
959 Route 46 East, 5th Floor, Parsippany, NJ 07054
Tel: 973-316-2700
8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631
Tel: 773-380-6000
2037 Bakers Mill Rd., Dacula, GA 30019
Tel: 678-546-9385
25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000
www.business.toshiba.com