

TOSHIBA

e-STUDIO™ 5516ACTG

e-STUDIO™ 7516ACTG

- > Color Multifunction Printer
- > Up to 75 PPM Color
- > Up to 85 PPM Black & White
- > Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Customizable UI



CONNECT. INTEGRATE. SIMPLIFY. AND MORE.

Technology for every workplace; delivering advanced functionality, ease of use, and peace of mind.

Every business is unique. That's why Toshiba offers the latest customizable solutions that can be tailored to meet your needs. Toshiba solutions help you simplify complex tasks while managing diverse information—efficiently and safely to maximize your productivity.

Our latest series delivers on our commitment to collaborate with clients in order to provide tailored, cost-effective solutions that meet your print, document management, and content needs while helping you meet your green objectives.

- > Speeds up to 55 & 75 PPM Color, 65 & 85 PPM Monochrome
- > High-resolution and high-volume color output
- > High-volume black & white output
- > Advanced e-BRIDGE Next technology
- > Fast dual-core processor



Simple, smart and stylish.

A larger 10.1" tablet-style touch screen with an embedded web browser is easy to use, and customizable to meet your needs, enhancing the sleek and modern look of the complete series.

Sleeker, faster, and more versatile than ever.

Toshiba's new sleek lineup is as impressive on the inside as it is on the outside. Its ultra-modern look houses the latest innovative technologies, like brilliant, multi-beam laser color at a speed of up to 75 pages per minute, and up to 85 pages per minute in monochrome.

- > 1,200 dpi x 1,200 dpi
- > High-speed, high-capacity Dual-Scan Document Feeder
- > Up to 600K maximum monthly copy volume

Elevate streamlines complicated multi-step processes into automated, one-touch functions.

We know you have work to do and at Toshiba we've introduced a new concept designed to make your job easier and more productive by personalizing the MFP user interface around your specific business processes.

Elevate enables customized and automated workflow presenting the user with convenient one-touch functions addressing only the tasks they use most. This results in simple operation and improved efficiency leading to an overall cost savings. Let Toshiba Elevate your productivity.

- > Customize and automate workflow specifically around your business processes
- > Boost productivity by reducing manual and paper intensive processes in the office
- > Personalize the user interface by department to deliver the utmost efficiency
- > Cost savings and greater efficiency through improved workflow and productivity
- > Clear away clutter and confusion on the homescreen by presenting only the tasks used most



INNOVATIVE FEATURES, VERSATILE CONNECTIVITY.

The Toshiba e-STUDIO5516ACTG/e-STUDIO7516ACTG helps workgroups connect, integrate and simplify while improving efficiency and productivity to facilitate collaboration between departments.

High Speeds include 55/75 brilliant color pages per minute and 65/85 monochrome pages per minute, respectively.

Advanced e-BRIDGE Next Technology enables the MFP to drive Toshiba's internally developed embedded solutions or those from a third party with ease.

Fast Dual-Scan Document Feeder handles up to 300 sheets at a time and seamlessly scans both sides of each page in a single pass to produce a max of 240 images per minute (IPM).

Auto Skew Correction ensures your scanned documents are reproduced accurately.

Fast First Copy Out Times include 6.4/5.4 seconds for full-color printing and 5.2/4.1 seconds (respectively) for black and white printing.

10.1" Tablet-Style Touch Screen works intuitively, helping you access instructions, functions, and commands with the swipe of the finger.

Banner Printing produces impressive signage as large as 12" x 47" using our unique AquaAce media.

Print Around eliminates printing bottlenecks by allowing other print jobs to go around a job that's held-up for a specific paper size, media type or color toner.

Saddle/Fold Capabilities offer saddle-stitch finishing and the option to fold without stapling.

e-BRIDGE Plus for USB lets you print PDF and JPG files straight from your USB drive and the MFP will scale documents to fit the available paper size if necessary.

Scan-to USB is great for capturing a file quickly when you're on the go.

Scan Preview allows you to review your scanned documents on the 10.1" tablet-style touch screen, even rotate and change pages prior to sending to file or email.

Fax Preview saves valuable resources by letting you view received faxes prior to printing them.

Notifications Feature takes the hassle out of checking for depleted supplies or maintenance needs.

Paper Volume Indicators on the front panel make it easy to see the paper sizes, types and levels in each cassette.



TOSHIBA INNOVATION AT ITS FINEST.

When it comes to seamless workflow and simplified integration, the e-STUDIO5516ACTG/e-STUDIO7516ACTG represents the finest Toshiba has to offer. The latest e-BRIDGE Next technology enables the systems to offer invaluable embedded solutions capabilities and third-party integration.

AirPrint® and Mopria® support address the printing needs of mobile device users, while Wi-Fi Direct simplifies access to the MFP. Toshiba's exclusive e-BRIDGE Print & Capture application enables users additional printing features and the ability to scan documents back to their tablets or smartphones.

Toshiba's V4 Driver with Toshiba Print Experience serves PCL users, a universal print driver and XPS support addresses Windows® environments while PS3 support provides connectivity for Macintosh® users and beyond.

Cloud Support

Toshiba's new e-BRIDGE Plus apps, including e-BRIDGE Plus for OneDrive® for Business, e-BRIDGE Plus for SharePoint® Online and e-BRIDGE Plus for Exchange Online let users print from Microsoft's cloud-based services directly at the front panel of the e-STUDIO MFP or their mobile device. This includes Word™, Excel® and PowerPoint® (docx, xlsx, pptx) documents stored in OneDrive® accounts or SharePoint® locations. When combined with our embedded OCR feature, documents can be scanned into popular Office™ formats as well.*

Toshiba's current e-BRIDGE multi-function printers are compatible with Microsoft Universal Print which enable customers to fully manage their print environment from Microsoft Azure. In addition, our e-BRIDGE Plus for Google Drive™, e-BRIDGE Plus for OneDrive®, e-BRIDGE Plus for DropBox®, and e-BRIDGE Plus for box™ offer scan and print solutions to the popular cloud storage destinations.*

*Your network settings and/or access control may vary depending on network environment when installing e-BRIDGE Plus applications. For details, please consult Toshiba's sales person.

Advanced Security

Even more important than functionality is the security offered by the e-STUDIO5516ACTG/e-STUDIO7516ACTG Series. Such technological advancements include:

- > A 320GB FIPS 140-2 Validated Self-Encrypting Drive (SED) with Automatic Data Invalidation (ADI) & Data Overwrite exceeds strict government requirements
- > IPsec is available to securely encrypt data sent to and from the MFP
- > HCD-PP Certified ensures that the MFP has met rigorous security assurance requirements to safeguard your digital documents

Environmental Responsibility

Because we have been working to protect the environment as well as your security, you can rest assured Toshiba has what it takes to protect both.

- > ENERGY STAR® V3.0 certified
- > RoHS compliance, the use of recycled plastics, and Super Sleep (0.6W) Mode work to help the environment
- > EPEAT Gold Registered for greener electronics, designed to help purchasers choose products that reduce environmental impact
- > The new e-STUDIO models' Typical [weekly] Electrical Consumption or TEC value is exceptionally low, equating to an environmentally friendly product with a low operating cost
- > e-BRIDGE Plus for Green Information provides users with a graphical display at the MFP of their environmental contribution to promote more effective use



IMPRESSIVE EVEN BEFORE YOU TURN IT ON.

1 Accessory Tray & Keyboard Options

GR1330 – Accessory Tray
GR9000 – Bluetooth Keyboard
GR1340 – 10-Key Numeric Keypad

2 Finishing Options

MJ1111B – 50-Sheet Console Finisher
MJ1112B – 50-Sheet Saddle Stitch Finisher
MJ6106N – Hole Punch Unit
KA6551 – Side Exit Tray

3 Connectivity Options

GD1370N – Fax Unit/2nd Line for Fax Unit
GN4020 – Wireless LAN/Bluetooth Module

4 Additional Paper Options

MP2502B – 2,500 Sheet Large Capacity Feeder

Additional Option Highlights

- > IPsec Security Enabler
- > Multi-Station Print Enabler
- > Parts #'s Embedded OCR Enabler



Toshiba's e-STUDIO5516ACTG/e-STUDIO7516ACTG offers the best of the best, enabling large workgroups to improve productivity and connectivity while simplifying the overall workflow.

Double the Scan Speed

A 300-sheet, high-speed, high-capacity Dual-Scan Document Feeder (DSDF) produces up to 120 IPM simplex and 240 IPM duplex.

Bluetooth/Wi-Fi Option

Bluetooth feature provides support for a wireless keyboard to simplify workflow processes at the MFP, while the Wi-Fi capability enables Wi-Fi Direct printing making it ideal for mobile users.

Volumes and Volumes

A high monthly copy volume of 480K/600K respectively. Impressive toner yields of 39,200 color and 106,600 black and white (each at 5%).

Multi-Station Print Enabler

Toshiba's internally developed Multi-Station Print Enabler allows users to send print jobs from their desktop and retrieve them at any available MFP by simply swiping their card and authenticating at that device.

Advanced e-BRIDGE Next Technology

Built on Linux®, this latest generation e-BRIDGE Next architecture features an Embedded Web Browser, an Intel Atom™ dual-core processor, 4GB RAM, and a 320GB FIPS 140-2 Validated SED enabling the MFP to easily drive Toshiba's internally developed solutions and third-party applications

e-STUDIO™ 5516ACTG/7516ACTG

Main Specifications

Copy System	Indirect Electrostatic Photographic Method/OPC/Laser Printing/ Heat Roller Fusing
Display	10.1" Color WSVGA Touch Screen Tilting Display
Copy Speed	Color: 55/75 PPM (LT), Monochrome: 65/85 PPM (LT)
First Copy Out	Color: 6.4/6.4/5.4, Monochrome: 5.2/4.5/4.1 Seconds
Warm-Up Time	Approx. 20 Seconds
Copy Resolution	600 x 600 dpi
Stack Feed Bypass	3.9" x 5.8" to 13" x 19", 12" x 47" Banner, Envelope
Multiple Copying	Up to 9,999 Copies
Paper Capacity	Tandem Drawer: Standard 3,520 Sheets/Max. 6,020 Sheets
Original Feed	Standard 300-Sheet DSDf
Scan Speed & Weights	DSDf Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color), Simplex: 9.3-110 lb Index, Duplex: 9.3-110 lb Index
Max. Original Size	LD
Paper Feed Sizes	Drawers: 540 Sheets-ST-R to 12" x 18" Integral Tandem LCF 1,160 x 2 LT-Only Stack Feed Bypass: 120 Sheets-3.9" x 5.8" to 13" x 19", 12" x 47" Banner Opt. 2,500-Sheet Ext. LCF LT-Only
Paper Weights	Tandem LCF 1,160 Sheets x 2-16 lb Bond-140 lb Index Plus 540 Sheets x 2-16 lb Bond-140 lb Index Stack Feed Bypass: 120 Sheets-16 lb Bond-110 lb Cover Opt. 2,500-Sheet Ext. LCF LT-Only -16 lb Bond-140 lb Index Standard Automatic Duplex Unit (16 lb Bond-140 lb Index)
Duplex	
Reproduction Ratio	25% to 400%
Max Duty Cycle	Max. 480K/600K Month (Color: 100%)
Weight	Approx. 470 lb
Approx. Dimensions	37.6" (W) x 27.5" (D) x 48.3" (H)
Toner Yield	CMY: 39,200, K: 106,600 @ 5%
Power Source	120 Volts, 50/60 Hz, 16 Amps
Power Consumption	Maximum 2.0kW (120V)
CPU	Intel Atom™ 1.75 GHz (Dual-Core)
Memory	4GB
Hard Disk Drive	320GB FIPS 140-2 Validated Self-Encrypting Drive

e-BRIDGE Next Print Specifications

PDL	PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG
Print Speed	Color: 55/75 PPM (LT), Monochrome: 65/85 PPM (LT)
Print Resolution	600 x 600 dpi (8 bit), 1,200 x 1,200 dpi (Color/2 bit) or 3,600 x 1,200 dpi (BW/with Smoothing) PS3 Only
Operating Systems	Windows® 8.1,10, Windows Server® 2012/R2, Windows Server® 2016, Macintosh® (macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, macOS 10.12, 10.13, 11.4), Unix®, Linux®
Network Protocols	TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for Novell® Environments, EtherTalk for Macintosh® Environments
Printing Protocols	SMB, LPR/LPD, IPP (Ver.2.0) w/Authentication, AppleTalk® PAP or, Port 9100 (Bi-Directional), NetWare P-SERVER LPD w/ iPrint, WS Print, FTP
Print Drivers	Windows® 8.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows Server® 2016, Windows® 10 (32-bit, 64-bit), macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, macOS 10.12, 10.13, 11.4
Interface	RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-Speed) Optional 802.11b/g/n, Wireless LAN, Optional Bluetooth
Wireless Device	AirPrint®, Mopria®, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple® App Store or Google Play)
Device Management	TopAccess, EFMS 6.3 (e-BRIDGE Fleet Management Software)
Account Control	Up to 10,000 Users or 1,000 Departments Supports User Authentication (on Device), Login Name/Password (via Windows® Domain) or Login Name/ Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function
Accessibility Features	Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen Timeout and Audible Beep Message Alerts

Security Features

User Authentication, On-Board Data Scramble Function, SCEP, Disable e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL/TLS (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IEC15408)* with HCD-PP v1.0, IEEE802.1X (Wired/Wireless), Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log Access Control for Job Log, Security Stamp, Role Based Access Control, Secure PDF, Digital Signature for Firmware Update, Integrity Check Function, Image Log, Card Authentication, NFC Authentication *Conformance with HCD-PPv1.0 in High Security Mode.

Environmental Stds. Certification

ENERGY STAR® (V3.0), EPEAT Gold WHQL (Windows® 8, 8.1, 10, 2008 R2, 2012, 2012 R2), Novell®, Citrix®, SAP, AirPrint®, Mopria®

Scan Specifications

Scan Speed	DSDf Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color)
Scan Modes	Standard: Full Color, Auto Color, Monochrome, Grayscale
Scan Resolution	600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi
File Formats	Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.) Color/Grayscale: JPEG, TIFF-Multi/Single Page, PDF-Multi/Single Page, Slim PDF, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.)
Image Compression	Color/Grayscale: JPEG (High, Middle, Low)

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	Up to 33.6 Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job
Scan Speed	0.7 Seconds Per Page, Maximum 73 IPM

e-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder/Box, 200 Pages Per Document

Accessories (Options)

Additional Paper Options	Meta Scan Enabler	GS1010	
Large Capacity Feeder	MP2502B	IPsec Enabler	GF1080
Finishing Options		Unicode Font Enabler	GS1007
50-Sheet Staple Finisher	MJ1111B	Embedded OCR Enabler	
Saddle-Stitch Finisher	MJ1112B	Per Seat License	GS1080NODE
Hole Punch Unit for MJ1111B/MJ1112B	MJ6106N	Multi-Station Print Enabler	
Side Exit Tray	KA6551	Per Seat License	GS1090NODE
Finisher Guide Rail	KN1103	e-BRIDGE Plus for OneDrive for Business V3.0	GB2300NODE
Connectivity/Security Options		e-BRIDGE Plus for SharePoint Online V3.0	GB2310NODE
FAX Unit/2nd Line for FAX Unit	GD1370N	e-BRIDGE Plus for Exchange Online V3.0	GB2320NODE
Wireless LAN/Bluetooth	GN4020	Miscellaneous Options	
Bluetooth Keyboard	GR9000	Accessible Arm	KK2550
Accessory Tray	GR1330	Harness Kit for Coin Controller	GQ1280
Panel 10-Key Option	GR1340	Manual Pocket	KK5008
Card Reader Holder	GR1320		
Fax Over IP License Key	GS1100NODE		



Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

Corporate Office

25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000

East Coast

959 Route 46 East, 5th Floor, Parsippany, NJ 07054
Tel: 973-316-2700

Midwest

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631
Tel: 773-380-6000

South

2037 Bakers Mill Rd., Dacula, GA 30019
Tel: 678-546-9385

West Coast

25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000

Web Site

www.business.toshiba.com